


# Installation Instructions Adaptor plate

400x400mm


## Component Checklist




### Tools Required:

10mm (3/8") socket wrench  
or Shifter

### Hardware



Nylock Nut (x4)



Washer (x4)

## IMPORTANT INFORMATION

**! IMPORTANT - Install 400x400mm Adaptor Plate as per Installation Instructions.**

! Compatible with Telehook: TH-1032-VFM, TH-1040-VFM, TH-1040-CTS, TH-1040-CTL, TH-1040-CT-B2B, TH-2040-VTR, TH-2250-VTP.

! This product supports a maximum load of 25kg (55lbs).


! This product supports VESA mounting hole patterns: 200x300mm, 200x400mm, 300x200mm, 300x300mm, 300x400mm, 400x200mm, 400x300mm, 400x400mm (see below for Mounting Configurations).

! The manufacturer accepts no responsibility for incorrect installation.

## Step 1. Check Components

Check you have received all parts against the Component Checklist and Hardware above.


## Step 2. Attach Adaptor Plates to Mounting Plate



### Mounting Configurations:


The Adaptor plates can be fixed vertically or horizontally.

Each configuration offers different VESA mounting hole configurations.



**VERTICAL**  
(most common)

400x400mm  
400x300mm  
400x200mm  
300x300mm  
300x200mm  
200x300mm



**HORIZONTAL**

400x400mm  
300x400mm  
300x300mm  
300x200mm  
200x400mm  
200x300mm

**INSTALLATION COMPLETE** - Refer to the Telehook product Installation Instructions.

